


Series 3 - T-17A cavity, Viton, cartridge seal kit

Model:
990-017-006



Technical Features

- The shelf life for this cartridge seal kit is twenty years from date of purchase. This date will be printed on the kit packaging.

Cartridge Installation Data

	U.S. Units	Metric Units
Cavity	T-17A	
Cartridge Thread	1"-14 UNS	
Valve Hex Size	1 1/4 in.	31,8 mm
Valve Installation Torque	150 - 160 lbf ft	200 - 215 Nm

990-017-006

What models can this kit be used on?

CBFA	CBGY	CNGD	FAHA	LOHB8	LRHA	PBHF	RVGA
CBFB	CCGA	CNGE	FBHA	LOHC	LRHB	PPHB	RVGB
CBFC	CCGG	CNGV	FREA	LOHCK	LRHC	PPHB8	RVGE
CBFD	CKGA	CNHE	FXEV	LOHCL	MBGA	PPHC	RVGF
CBFG	CKGB	COHA	LKHA	LOHCZ	MBGAX	PPHE	SCGA
CBFH	CKGC	COHB	LKHB	LOHD	MBGB	PPHF	SQHB
CBFL	CKGD	COHC	LKHC	LOHD8	MBGBX	PPHF8	XHBA
CBGA	CKGE	CXGE	LKHD	LOHDL	MBGG	PRHB	XHCA
CBGB	CKGF	CXHC	LOGC	LOHO	MBGGX	PRHR	XHOA
CBGG	CKGG	DKHC	LOGCZ	LPHA	MBGM	RSHC	XHOB
CBGH	CKGH	DKHD	LOHA	LPHA8	PBHB	RSHC8	XHOC
CBGL	CKGI	DOHC	LOHA8	LPHC	PBHB8	RSHE	XHOCB
	CKGV	DOHD	LOHB	LPHCL	PBHC	RSHH	

Display Components

	Description	Quantity	View
500-101-120	O-Ring	1	C
500-101-126	O-Ring	1	A
500-102-124	O-Ring	1	B
515-102-121	Backup Ring	2	C
515-102-123	Backup Ring	1	B
515-102-126	Backup Ring	1	A

Instructions/Notes

- Install back-up rings and O-rings as shown in views.
 - When installing continuous back-up rings, use the same technique and the same care used to install O-rings.
 - When installing cartridge - be sure to torque to recommended value.
-
-